



# The Ohaus FD Food Portioning Scale – Speed, Durability and Cleanliness Designed for Food Service Use

The Ohaus Food Portioning Scale is a rugged, multi-use portioning scale designed for use in food service applications. Ideally suited for food portioning and checkweighing, the FD Food Portioning Scale combines an easily cleaned design, fast display and high precision loadcell. Designed for use in restaurants, bakeries, food manufacturing and other areas requiring fast operation and flexibility, the Ohaus Food Portioning Scale offers durability and cleanliness in one economical design.

### Standard Features Include:

- · All-stainless steel construction
- NSF Certified and supports HACCP compliance
- · Checkweighing mode with 3 LED indicator and audible alarm
- Bright backlit LCD display
- Stable weight display within 2 seconds
- Multiple weighing units including kg, g, lb, decimal and fractional oz and lb:oz
- Internal rechargeable battery or AC power
- Industry leading support

# The Ohaus FD Food Portioning Scale

## **Easy to Set-Up for Your Operation:**


The Ohaus FD Food Portioning Scale Has All The Features You Need:

- **Selectable Weighing Units** The FD Food Portioning Scale can be set up to display all, some, or only one weighing unit to match the requirements of your operation.
- Lb & Oz Display The FD Food Scale can display a decimal pound to 3 decimal places, as well as fractional or decimal ounces, and can even display results in a combined lb:oz display.
- Metric Display For metric use, the FD Food Scale can display results in kilograms or grams with a readability ranging from 0.5g to 2 g, depending on model.
- Change Units Quickly The unit displayed can be changed with a single key press
- Set It Up and Lock It In The FD Food Portioning Scale can be set to the mode and weighing units required, and then locked-in using either software or hardware locks. The Ohaus FD Food Portioning Scale can be locked to ensure the configuration you choose is the configuration you use!
- Easy to Calibrate The FD Food Portioning Scale's software menu allows the user to recalibrate the FD Scale to ensure accurate results. To prevent accidental recalibration, the FD Food Portioning Scale also can be configured using software and hardware calibration lockouts. The user can calibrate the FD scale using either span (two-point) or linear (three point) calibration setups.
- Legal-For-Trade Modes Included For operations that require OIML approval, the Food Portion Scale includes legal-for-trade type approval software.

## For Checkweighing Applications, The Ohaus FD Can Be Quickly Configured:

The FD Portioning Scale can be set to either simply display a weight, or can be set to act as a dedicated, low-profile checkweigher for food portioning and grading:

- **Portioning and Prepackaging** With the positive checkweighing method for packaging, add to the portion on the pan until you reach the weight you need
- **Portioning Out of the Box** Use the negative checkweighing method for portioning and pizza making, portioning out of a container on the pan until the required weight is reached
- Sorting & Grading The "zero" checkweighing method is designed for sorting and grading operations, so you can check portions against preset limits
- Quickly Set Targets Target weights can be entered quickly using the dedicated Setpoint key
- Bright LED's and Buzzer Speed Use Progress against weight targets can be indicated with the three LED's, with indications for Over, Accept and Under with selectable audible buzzer.



### **Designed for Food Service Use:**

Fast, Easy-To-Read Display – The FD Food Portioning Scale is designed to clearly and guickly display weighing results:

- Large, backlit LCD display
- Fast display updates within 2 seconds
- Bright LED indicators for Checkweighing mode
- Text display of weight units no cryptic unit designations or hard-to-read annunciators
- Audible buzzer alerts user when limits are reached
- · Battery power level indicator
- Bright annunciators for scale stability, center of zero, net and tare weights, checkweighing mode indication



- . Manual taring using the large, dedicated Tare key
- The FD can be set-up to automatically tare the first weight placed on the pan
- For hands-free operation, the FD scale can also be tared using the optional foot switch



## The Ohaus FD Food Portioning Scale

tem Number	FD3	FD6	FD15
Shipping Weight	5 kg		
Net Weight	3.6 kg		
Shipping Dimensions WxHxD	400 x 320 x 185 mm		
Scale Dimensions WxHxD	300 x 223 x 71 mm		
Pan Size	209 x 209 mm		
Operating Temperature and Humidity Range	-10° to 40°C, 10 to 85% relative humidity, non-condensing		
Calibration	User-selectable external span or linearity calibration		
Battery	Internal rechargeable sealed lead-acid battery with 120 hours continuous use		
AC Power	9 VDC 0.5A AC Wall Adapter100-120 V AC, 50/60 Hz		
Overload Capacity	150% of capacity		
Auto-Zero Tracking	Off. 0.5. 1 or 3 divisions		
Stabilization Time	< 2 seconds		
Tare Range	Full Capacity by Subtraction		
Environmental Protection	IP 43		
Keyboard	4 – button membrane switch		
Checkweighing Indicators	3 LED (yellow, green, red) with configurable operation and alert beeper		
Display Indicators	Stability, center of zero, tare or net weight, battery status, checkweigh mode		
Display	19mm high 5-digit, 7-segment backlit blue LCD display		
Application Modes	Weighing, Checkweighing		
Weighing Units	gram, kilogram, pound, decimal ounce, ½, ½, and ¼ fractional ounce, combined lb:oz display (either decimal or fractional ounces)		
Linearity (G) Maximum Displayed Readability	± 0.5g	± 1g	± 2g
Repeatability (Std. Dev.) Maximum Displayed Readability	0.5g	1g	2g
Capacity x Readability Legal-For-Trade Mode Readability*	3000 g x 1 g 6 lb x 0.002 lb 96 oz x 0.05 oz or 1/4 oz	6000 g x 2 g 6000 b x 0.005 lb 240 oz x 0.1 oz or 1/4 oz	15 kg X 0.003 kg 15000 g x 5 g 30 lb x 0.01 lb 480 oz x 0.2 oz or 1/4 oz
Capacity x Readability Maximum Displayed Readability	6 lb x 0.001 lb 96 oz x 0.02 oz or <sup>1</sup> / <sub>4</sub> oz 6 lb:0 oz x 0.1 oz or <sup>1</sup> / <sub>4</sub> oz 3 kg x 0.001 kg	15 lb x 0.002 lb 240 oz x 0.05 oz or <sup>1</sup> / <sub>4</sub> oz 15 lb:0 oz x 0.1 oz or <sup>1</sup> / <sub>4</sub> oz 6 kg x 0.002 kg	30 lb x 0.005 lb 480 oz x 0.1 oz or <sup>1</sup> / <sub>4</sub> oz 30 lb:0 oz x 0.1 oz or <sup>1</sup> / <sub>4</sub> oz 15 kg x 0.005 kg
	3 kg x 0.0005 kg 3000 g x 0.5 g	6 kg x 0.001 kg 6000 g x 1 g	15 kg x 0.002 kg 15000 g x 2 g

<sup>\*</sup> lb:oz display unit not available in legal-for-trade application mode.

### **Physical Features**

Stainless steel top and bottom housings, dishwasher safe stainless steel pan, backlit LCD display, rubber user-adjustable leveling feet, front panel leveling bubble, internal rechargeable lead-acid battery, external AC wall adapter, weight/mode stability/center of zero/net weight/tare weight/text unit indication, 4-bar battery status indicator with low-battery warning, 3 LED's and buzzer for use in checkweighing mode, dedicated tare key, audible buzzer with user-selectable volume control, selectable scale auto-off, sealable scale configuration and calibration lockout switch.

### **Operational Features**

Selectable environmental averaging settings, backlight control with auto-off option, selectable weighing units, configurable checkweighing mode, configurable software lockout menu, span or linearity calibration in kg or lb unit with optional external masses, semi-automatic or automatic tare, selectable auto-zero tracking.

#### **Accessories**

Foot switch (p/n 71169633).

### **Approvals**

- Food Service: NSF Listed/Certified to NSF C-2 -- Special Equipment and/or Devices (Food Service Equipment); meets requirements for HACCP conformity; USDA-AMS accepted.
- Electrical/Emissions: UL C US listed, meets AS/NZS4251.1 Emission/AS/NZS4252.1 Immunity, FCC Class B Part 15 operation, Industry Canada Class B.
- Type/Legal-for-Trade: OIML R76 Class III and EC Type Approval.
- Quality: Ohaus quality management system registered to ISO 9001:2000

### **Ohaus Corporation**

\* 19A Chapin Road P.O. Box 2033 Pine Brook, NJ 07058 USA

Tel: 973.377.9000 Fax: 973.593.0359

www.ohaus.com

With offices throughout Europe, Asia, and Latin America

\* ISO 9001:2000 Registered Quality Management System



Copyright Ohaus Corporation